



Technical Data	S 20	S 26
Speed range [1/min]	100 - 1100	60 - 1100
Type of movement	orbital	orbital
Shaker orbit [mm]	3.0	3.0
Timer	Yes	Yes
Display	-	backlight LCD
Interface	-	RS232
Permissible load of platform, max. [kg]	3.0	1.5
Power supply [V]	See: order information	See: order information
Weight [kg]	4.1	6.9
Dimensions [WxDxH mm]	145 x 180 x 130	280 x 170 x 245
Protection class according to DIN EN 60529	IP 32	IP 32

Order Information	Part Number	
230 VAC / 50Hz, EU plug (Type F)	60283-0000	60386-0000
115 VAC / 60Hz, USA plug (Type B)	60283-0001	-



Accessories	Part Number	Description
S – Shaking adaptor	60648-0000	Shaking platform 200x400 mm with special adhesive mat. Recommended maximum shaking speed: 1000rpm. Dimensions: 370x150x45 mm
U – Shaking adaptor	60686-0000	Universal shaking adaptor for Erlenmeyer flasks and other bottles and containers. Recommended maximum speed: 500rpm. Dimensions: 350x150x125 mm
V – Shaking adaptor	60685-0000	Shaking adaptor for 4 Erlenmeyer Flasks or round-bottom flasks (500ml) Recommended maximum speed: 500rpm. Dimensions: 370x150x45 mm
R – Shaking adaptor	60687-0000	Test tube shaking adaptor for shaking up to 36 test tubes up to 16mm diameter. Recommended maximum speed: 800rpm. Dimensions: 190x140x145 mm
E – Shaking adaptor	60683-0000	Shaking adaptor for single hand held vessels up to 100ml. Recommended maximum speed: 1000rpm. Dimensions: 137x132x44 mm
2E - Shaking adaptor	60689-0030	Shaking adaptor for 2 Erlenmeyer flasks 1000 ml
4E - Shaking adaptor	60689-0020	Shaking adaptor for 4 Erlenmeyer flasks 500 ml
6E - Shaking adaptor	60689-0010	Shaking adaptor for 6 Erlenmeyer flasks 250 ml
RS232 extension cable	30275-0051	RS 232 extension cable 1.8 m
USB to RS232 adaptor	30244-0001	USB adaptor for connection PC to RS232 interface of shaker