

STANDS

| Sales No. | Product | Description |
|-----------|---------------|---|
| 11040013 | ST-P 15 / 320 | Stainless steel stand with base, height-adjustable bracket for supporting the drive and base mounting. Weight: 1.00 kg |
| 11040012 | ST-P 01 / 200 | Stainless steel hinge stand (gas spring) and base mounting. The drive support can be rotated in any direction. It can be raised or lowered. Weight: 3.60 kg |
| 11040011 | ST-P 22 / 600 | Plate stand with two support rods. Optional: Vessel holder with boss head clamp (11045011), Safety ring (11045031), Weight: 4.00 kg |



USING THE RIGHT DISPERSING VESSEL

The proper selection of the dispersing aggregate is crucial for the result of your application. Choosing the right process vessel makes all the difference how quickly and effective results can be produced. Our specially developed GD glasses in their typical cloverleaf shape break the flow of the product. This increases the turbulences inside the vessel, thus reducing the processing time significantly.

You may select from a variety of vessels made of borosilicate glass; with or without lid, with sealed feedthrough or with different processing volumes.

Our borosilicate glass dispersing vessels are made of highly chemical- and temperature-resistant and resilient glass. It is mainly used in laboratories and where ever chemical processes are applied.

| Sales No. | Product | Ø/H (mm) | Process volume | Thickness | Thread | Description |
|-----------------------------------|-----------|----------|----------------|-----------|--------|-------------|
| Open on top | | | | | | |
| 11051010 | GS 15 | 30/100 | 35 ml | 2.8 mm | - | - |
| 11051011 | GS 25 | 54/150 | 150 ml | 3.5 mm | - | - |
| With screw cap and sealing | | | | | | |
| 11051020 | GS 15K | 30/100 | 35 ml | 2.8 mm | GL25 | - |
| 11051021 | GS 25K | 54/150 | 150 ml | 3.5 mm | GL45 | - |
| Incl. cover with sealing and hole | | | | | | |
| 11051030 | GS 15KL08 | 30/100 | 35 ml | 2.8 mm | GL25 | 8 mm hole |
| 11051031 | GS 15KL12 | 30/100 | 35 ml | 2.8 mm | GL25 | 12 mm hole |
| 11051040 | GS 25KL12 | 54/150 | 150 ml | 3.5 mm | GL45 | 12 mm hole |
| 11051041 | GS 25KL20 | 54/150 | 150 ml | 3.5 mm | GL45 | 20 mm hole |