
Filtration Accessories











| Specification | 1200 ml, PES vacuum bottle | 1200 ml, PC vacuum bottle |
|--------------------------|----------------------------|---------------------------|
| Catalog number | 197000-11 | 197000-11-PC |
| Graduated increment | 100 ml | 100 ml |
| Overflow protection | Yes | Yes |
| Cap with suction fitting | Yes | Yes |
| Hose barb | ID8 | ID8 |
| Autoclavable | Yes | Yes |

PP Heavy-Duty Vacuum Bottle NEW

| Specification | 4000 ml, PP vacuum bottle | 4000 ml, PP vacuum bottle with drain |
|---------------------|---------------------------|--------------------------------------|
| Catalog number | 197200-47 | 197200-48 |
| Connector | Hose barb | Hose barb |
| Graduated increment | 500 ml | 500 ml |
| Overflow protection | Yes | Yes |
| Hose barb | ID4 ~ ID8 | ID4 ~ ID8 |
| Drain device | - | Yes |
| Autoclavable | Yes | Yes |

Multilayer Filtration Adaptor NEW

| Specification | Multilayer filtration adaptor |
|------------------------------|---------------------------------------|
| Catalog number | 167230-05 |
| Main material | Borosilicate glass |
| Material of membrane support | SS screen |
| Filter diameter | 47 mm |
| Filter holder | 300 ml glass filter holder (optional) |

| Continuous Filtration Kit NEW | | |
|-------------------------------|---------------------------------------|-------|
| Specification | Continuous filtration kit | VIDEO |
| Catalog number | 167210-36 | |
| Main material | PTFE | |
| Material of hose barb | PTFE | |
| Filter holder | 300 ml glass filter holder (optional) | |
| Hose barb | ID6 | |
| | | |

* PES : Polyethersulfone, PC : Polycarbonate, PP : Polypropylene

Filtration Accessories





| specification |
|-------------------|
| Catalog numbe |
| Brand |
| Filter diameter |
| Pore size |
| Material of filte |
| Package |



Catalog numbe Material of cap Material of gask Stopper Hose barb

Autoclavable

Specification

Application for GL45 Suction Cap


Waste Bottle

Suitable for collecting waste media by using GL45 bottle in connection with suction pump and accessories.



Vapor Absorption (Neutralization) Bottle

Ideal for absorbing acid or alkaline vapor to prevent harmful vapors from spreading into the environment or pump.





Membrane Filters

| | Glass fiber filter | MCE membrane |
|----|--------------------|---------------|
| er | 167100-20 | 167100-52 |
| | Pall | Pall |
| | 47 mm | 47 mm |
| | 1µm | 0.45µm |
| r | Glass fiber | MCE |
| | 100/PK | 200/PK |
| r | 100/PK | MCE 200/PK |

GL45 Suction Cap / Filtration Adaptor

| | GL45 suction cap | GL45 filtration adaptor |
|-----|------------------|-------------------------|
| er | 197000-60 | 197000-65 |
|) | PP | PP |
| ket | - | PTFE |
| | - | No.8 stopper |
| | ID6 | ID4 ~ ID8 |
| | Yes | Yes |

Moisture Trap Bottle

Available to absorb moisture with desiccant which turns pink when saturated.



Safety Bottle

Works as a safety bottle to prevent liquid from being sucked into pump.



* Please refer to P.66 to select GL45 Laboratory Glass Bottle