SENSORS

Polilyte Plus family



For more specifications see www.hamiltoncompany.com

Specifications

Measuring range
Process temperature

Pressure range (relative to ambient)

Hygienic aspects

Reference system

pH glass Electrolyte

Diaphragm

O-ring

0 to 14 pH

CIP: HB, PHI SIP: H, HB, PHI See table on page 18

Polisolve Plus

Single Pore EPDM: HB, PHI

FKM: H, HF

Everef-L

See table on page 158/159 See table on page 158/159

Autoclavable: H, HB, PHI

The outstanding success of the Polilyte Plus in chemical and wastewater applications gave the inspiration for transferring the good features to a whole family of sensors. The expanded portfolio widens the range of applications that can be covered.

All members have the same reference electrolyte Polisolve Plus, use the Single Pore technology but will have different pH glasses. A new member with the HB glass will be established.

Benefits

- ► More applications with HB pH glass
- ▶ Better overview of the portfolio
- ► There's always at least one family member that suits the different applications
- ► Resistant against solvents, strong acids and bases

Typical applications

- Sugar industry
- Microelectronics
- ► Industrial wastewater
- Downstream processes
- Fermentation







How to choose the sensor	New sensor	pH glass	Electrolyte	Predecessor	
HF in the media, low temperature	Polilyte Plus HF	HF	Polisolve Plus	ClaryTrode	
Low conductivity	Polilyte Plus H	Н	Polisolve Plus	Polilyte HT	
CIP, SIP, autoclavations, chemical robustness	Polilyte Plus PHI	PHI	Polisolve Plus	Polyclave	
CIP, SIP, autoclavations, fast response time	Polilyte Plus HB	НВ	Polisolve Plus		
High pressure	Polilyte Plus XP	Н	Polisolve Plus	Polilyte Plus XP	

Ordering Information

242428	Basic number = Polilyte Plus VP 120 (old Ref)					
	Code	pH glass				
	1	Н				
	2	HB (not for MS)				
	3	HF				
	4	PHI				
		Code	Electric	cal Conne	ector	
		1	VP 🚱			
		2	S8 6 Arc			
		3				
		4 Memosens 6				
			Code	a-leng	th (mm)	
			1 120			
		2 225				
			3	325		
		4 360 (not for Arc, MS only with H glass)			t for Arc, MS only with H glass)	
			5 425			
				Code	Temperature sensor	
				1	Pt100 (VP) (not applicable for Arc)	
				2	Pt1000 (VP) (not applicable for Arc)	
	+	+	+	3	none (S8) or given (Memosens, Arc)	
242428 –					← Order Code	
238811	Dolilyte	Plus XP	20.400			



Accessories

pH buffers see page **▶** 106

Cables see page ▶ 112

Housings see page **▶** 127

