Order information and accessories.

Authorized extension of your system.

Our modular accessories provide the at most flexibility. Switching grinding attachments is as easy as changing sieves. Our application experts are available to answer your questions at any time.

MILL



Sales No.	Product	Description
Mill with han	nmer grinding attachment	
35010020	PX-MFC 90 D, 230 V	CH-power cable, hammer attachment, sieve 2.0 mm, tool set, rack for tubes with 12 intercepting tubes
35010021	PX-MFC 90 D, 230 V	EU-power cable, hammer attachment, sieve 2.0 mm, tool set, rack for tubes with 12 intercepting tubes
35010022	PX-MFC 90 D, 230 V	UK-power cable, hammer attachment, sieve 2.0 mm, tool set, rack for tubes with 12 intercepting tubes
35010023	PX-MFC 90 D, 100 - 120 V	Power cable, hammer attachment, sieve 2.0 mm, tool set, rack for tubes with 12 intercepting tubes
Mill with blac	de grinding attachment	
35010030	PX-MFC 90 D, 230 V	CH-power cable, blade grinding attachment incl. dismounting tool, sieve 2.0 mm, tool set, rack for tubes with 12 intercepting tubes
35010031	PX-MFC 90 D, 230 V	EU-power cable, blade grinding attachment incl. dismounting tool, sieve 2.0 mm, tool set, rack for tubes with 12 intercepting tubes
35010032	PX-MFC 90 D, 230 V	UK-power cable, blade grinding attachment incl. dismounting tool, sieve 2.0 mm, tool set, rack for tubes with 12 intercepting tubes



STODGER

35010033

Sales No.	Product	Description
35080001	Stodger	For active insertion of fibrous materials, which do
		not reach the grinding chamber due to their weight.

Power cable, blade grinding attachment incl. dismounting tool, sieve 2.0 mm,

tool set, rack for tubes with 12 intercepting tubes





Sales No.	Product	Description
35080004	Intercepting tubes	12 intercepting tubes for PX-MFC 90 D
35080003	Rack for tubes	Rack with a drawer for 12 intercepting tubes