

# IKA

designed for scientists



## C-MAG HS 4 digital

/// Data Sheet

Magnetic stirrer with heating and ceramic heating plate which offers excellent chemical resistance.

- Powerful motor for stirring quantities of up to 5 l (H<sub>2</sub>O)
- Simultaneous digital display of target and actual temperatures via LCD display
- Directly connection for a PT 1000 temperature sensor enable a precise temperature control (included in delivery)
- Control accuracy in medium +/- 0,5 K (in combination with PT 1000)
- Display of actual temperature value in medium with 0,1 K resolution when using PT 1000 temperature sensor
- 3 operating modes to choose (standard, safe, adjustment protection)
- Fixed safety circuit of 550 °C

[www.ika.com](http://www.ika.com)

Subject to technical changes



IKAworlwide



IKAworlwide /// #lookattheblue



@IKAworlwide



designed for scientists

- Hot Top indicator >> hot surface warning to prevent burns!
- Digital error code display
- Elevated control panel for protection against leaking liquids





designed for scientists

## Technical Data

Number of stirring positions	1
Stirring quantity max. per stirring position (H <sub>2</sub> O) [l]	5
Motor rating output [W]	1.5
Direction of rotation	left
Speed adjustment	scale 0 - 6
Speed range [rpm]	100 - 1500
Stirring bar length max. [mm]	30
Self-heating of the set-up plate by max. stirring (RT:22°C/duration:1h) [K]	+1
Heat output [W]	250
Temperature display set-value	LCD
Temperature display actual-value	LCD
Heating temperature range [°C]	50 - 500
Heat control	stepless
Temperature setting resolution of heating plate [K]	5
Connection for ext. temperature sensor	PT1000
Fixed safety circuit [°C]	550
Set-up plate material	ceramic
Set-up plate dimensions [mm]	100 x 100
Heating rate (1l H <sub>2</sub> O in H1500) [K/min]	2.5
Dimensions (W x H x D) [mm]	150 x 105 x 260
Weight [kg]	3.566
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 21
Voltage [V]	120
Frequency [Hz]	50/60
Power input [W]	270