

2/3/5L Erlenmeyer Flasks

For Large Scales, Suspension cells

2/3L PC Erlenmeyer Flasks, Flat-bottom




Seal Cap Cat.No.	Vent Cap Cat.No.	Volume	Dimension (mm)			/Case
			Height	Neck O.D.	Bottom Dia	
785001	785011	2L	285	47	162	6
786001	786011	3L	253	62	230	4


2/3/5L PC High Efficient Erlenmeyer Flasks



High Efficient Erlenmeyer Flask VS Erlenmeyer Flask



3L High Efficient Erlenmeyer Flask



3L Conical Erlenmeyer Flask

Take 3L high efficiency erlenmeyer flask and 3L conical erlenmeyer flask as example:

- For the same shaker, more 3L high Efficient Erlenmeyer flask can be placed on, greatly saving space.
- The breathable membrane of the high efficient Erlenmeyer flask cap is bigger, which enables a higher oxygen flux.
- Equipped with Transfer Cap, safer and convenient.