## **Selection Menu**

# **Set-up Accessories**

#### **GUI** Resistive Touch Control

- Operate with a gloved hand
- Large visibility of settings
- Speed control on home screen


#### **Settings Menu**



#### **Torque Timer Menu**



For full specifications CaframoLabSolutions.com



#### A129 Plate Mount

- 260 x 100 mm (10 x 4 in)
- 6.4 mm (¼ in) thickness
- 304 electropolished stainless steel

Sturdy simple mounting solution. Secure to existing horizontal surfaces, mixing equipment, drum brackets or industrial stands. Slotted bolt pattern provides adjustability when mounting.



Download template for mounting.

### A128SET C-Clamp Set

- Single bolt adjusts angle on two axes
- Attaches directly to a drum, frame or stand
- Cast 304 electropolished stainless steel

Mount the Caframo Crossover mixer to any stable vertical including an industrial stand, drum or vessel. Easy single bolt adjustment for multi-angle positioning. Set includes c-clamp, clamp adapter and

hardware. Standard tool installation.

## **A118** Stand with Casters

- Adjustable 99 to 145 cm (39 to 57 in) height
- 102 x 102 cm (40 x 40 in) caster footprint
- Plate steel, square tube construction

This manual lift, heavy duty stand and base provides a solid mount for the Caframo Crossover when mixing in drums or tanks up to 122 cm (48 in) in diameter. This stand comes with smooth rolling casters that swivel and lock in place.

