

# ORBi-SHAKER™ CO<sub>2</sub>

## All Environment Shaker

Microplate Model (3mm Orbit)



- + *Designed for use in CO<sub>2</sub> Incubators and other extreme environments*
- + *Remote control, adjust settings without exposing chamber*
- + *Compact, 3mm orbit for thorough mixing of well plates*
- + *Includes 6 position microplate platform*

The new Orbi-Shaker CO<sub>2</sub>-MP is designed for thorough, mixing of microplates in extreme environments, including CO<sub>2</sub> incubators. It can withstand temperatures from 0 to 65°C and humidity levels up to 100%.

To avoid contamination, unintentional release of gas or deviations from protocol, both speed and time are set via the included remote control module. The remote controller can magnetically mount to the outer walls of the incubator and allows the user to set and adjust the shaker settings without opening the chamber door(s).

A 6 position microplate platform is included and secures both standard or deep well plates

### Technical Data

Speed Range:	200 to 1200 rpm
Speed Increment:	1 rpm
Orbit:	3mm
Max. Capacity:	6 x microplates
Platform Dimensions:	
Included (Microplate):	12 x 13 in. / 33 x 30 cm
Operating Temp.:	0° to 65°C
Max. Humidity:	100%
Weight:	24.5 lbs / 11.1 kg
Dimensions:	
Shaker:	11.8 x 13.5 x 3.5 in. / 30 x 34 x 9 cm
Remote Control:	7.2 x 6.7 x 3.5 in. / 18 x 17 x 9 cm
Cord Length:	60.5 in. / 154 cm
Electrical:	120V OR 230V, 50-60Hz, 600W

Also Available...

**ORBi-SHAKER™ CO<sub>2</sub>**  
19mm orbit



Ideal for TC and Erlenmeyer Flasks

### Ordering Information

**BT4500\*** Orbi-Shaker CO<sub>2</sub>-MP, All Environment Shaker with remote control, includes 6 position microplate platform, 115V

\*To order item in 230V, add (-E) to item number.

**Benchmark**   
Scientific

PO Box 709 Edison, NJ 08818  
Phone: 908-769-5555 Fax: 732-313-7007  
Web: [www.BenchmarkScientific.com](http://www.BenchmarkScientific.com)  
Email: [Info@BenchmarkScientific.com](mailto:Info@BenchmarkScientific.com)