

Cat. No	Description	Articles
---------	-------------	----------

DAIHAN-brand® 1.5~50ml Popular Classic Centrifuge “Cef”, Safety Balance, 3000- & 6000-rpm, Economy Model with 6- & 8-Holes, or 12- & 24-Holes(in 50ml Model) Fixed Angle Rotor, 1.5~50ml 튜브용 경제형 원심분리기



2-Year Warranty

I. “Cef-6” for 6 Tubes of 1.5~15ml, with 6 Holes Fixed Angle Rotor, 3000rpm



2-Year Warranty

II. “Cef-8” for 8 Tubes of 1.5~15ml, with 8 Holes Fixed Angle Rotor, 6000rpm



2-Year Warranty

III. “Cef-50.6” for 6 Tubes of 50ml, with 6 Holes Fixed Angle Rotor, 4000rpm

- DAIHAN Designed
- Speed is Linear and Stables
- Interchangeable Rotor
- Ideal for Biology, Medicine, Pharmacology, Laboratory, etc. Various Application
- with 6- & 8-Holes or 12- & 24-Holes Fixed Angle Rotor for 1.5ml ~ 50ml Tubes ; On Adapters Adjustable 1.5/2ml, 5~7ml, 10~15ml, and 50ml

- * The Design is up-to-date, Beautiful Outlook and Durable
- * Auto-balancing System
- * Stepless Controller : Speed and Operating Time
- * ABS Outer Shell can Resist Collision.
- * with Safety Switch when Centrifuge Lid Opened the Motor can be Stop

Specifications & Ordering information

Spec.	Model	I. 15ml “Cef-6” 6 Holes - 1.5~15ml	II. 15ml “Cef-8” 8 Holes - 1.5~15ml	III. New 50ml “Cef-50.6” 6 Holes - 50ml or 12/24 Holes - 1.5~15ml
		Fixed Angle Rotor&Capa.	Included 6Hole ; (1.5~15)ml Tubes Option	8Hole ; (1.5~15)ml Tubes
Useful Tube size & Acceptance	6 Tubes ; 10~15ml, 1.5~7ml on Adapters	8 Tubes ; 10~15ml, 1.5~7ml on Adapters	(1) 6 Tubes ; 50ml When option Rotor ; (2) 12 Tubes ; 10~15ml (3) 24 Tubes ; 10~15ml 1.5~7ml on Adapters	
Adapter and Size	Included ② 6ea×10~15ml Tubes Size ; id17.5×L95mm Option ③ 6ea×5~7ml Tubes Size ; id13.5×L69mm ④ 6ea×1.5/2ml Tubes Size ; id11×L42mm	② 8ea×10~15ml Tubes Size ; id17.5×L95mm Option ③ 8ea×5~7ml Tubes Size ; id13.5×L69mm ④ 8ea×1.5/2ml Tubes Size ; id11×L42mm	① 6ea×50ml Tubes Size ; id30.7×L104mm ② 12/24ea×10~15ml Tubes Size ; id17.5×L95mm ③ 12/24ea×5~7ml Tubes Size ; id13.5×L69mm ④ 12/24ea×1.5/2ml Tubes Size ; id11×L42mm	
Speed Range (rpm)	300~3000rpm at 60Hz (300~2500rpm at 50Hz)	300~6000rpm	600~4000rpm	
R.C.F	1,066×g	4,265×g	2,325×g	
Display	None	Tachometer for Speed & R.C.F	None	
Timer	0~30min Analog Timer			
Motor	Induction Motor	DC Motor		
Safety Manual Brake	None	Yes	None	
Dimension & Weight	280×280×h255mm, Net. 3.5kg, Gross. 4kg	280×280×h265mm, Net. 4.5kg, Gross. 5kg	300×300×h315mm, Net. 8.5kg, Gross. 9kg	
Electric Reqts	AC 230V, 50/60Hz or AC 120V, 60Hz			

Cat. No.	230V	DH.Cef0006	DH.Cef0008	DH.Cef0010
		120V	DH.Cef0106	DH.Cef0108
Price, Each. ₩				

Spare Rotor and Tube Adapters

- DH.CefR5006 (1) 50ml 6Holes Angle Rotor “R5006” with 6ea×50ml Tube Adapter PP “TA50”, idφ30.7×L104mm, for “Cef-50.6” & “Cef-D50.6”
- DH.CefA050 ① 50ml Tube Adapter PP “TA50”, idφ30.7×L104mm, Fit to Rotor “R5006”, for Centrifuge “Cef-50.6” & “Cef-D50.6”
- DH.CefA015 ② 10~15ml Tube Adapter PP “TA15”, idφ17.5×L98mm, for Centrifuge “Cef-6” & “Cef-8”, and Rotor “R1512” & “R1524”

Ea. Price, ₩

Optional Rotor and Tube Adapters

- DH.CefR1512 (2) 10~15ml 12Holes Angle Rotor “R1512”, with 12ea×10/15ml Tube Adapter “TA15”, idφ17.5×L98mm, for Centrifuge “Cef-50.6” & “Cef-D50.6”
- DH.CefR1524 (3) 10~15ml 24Holes Angle Rotor “R1524”, with 24ea×10/15ml Tube Adapter “TA15”, idφ17.5×L98mm, for Centrifuge “Cef-50.6” & “Cef-D50.6”
- DH.CefA007 ③ 5~7ml Tube Adapter PP “TA7”, idφ13.5×L69mm, Fit to “TA15”, Tube Adapter, for Centrifuge “Cef-6”, “Cef-8”, “Cef-50.6”, and “Cef-D50.6”
- DH.CefA002 ④ 1.5/2ml Tube Adapter PP “TA2”, idφ11×L42mm, Fit to “TA15”, “TA1503” Tube Adapter, for Centrifuge “Cef-6”, “Cef-8”, “Cef-50.6”, and “Cef-D50.6”

Ea. Price, ₩



①TA50
(1) Fixed Angle Rotor ; 50ml 6Holes, “R5006”



②TA15
(2) Fixed Angle Rotor ; 10~15ml 15Holes, “R1512”



②TA15
(3) Fixed Angle Rotor ; 10~15ml 24Holes, “R1524”



①TA50 ②TA15 ③TA7 ④TA2
Optional Tube Adapters