

DAIHAN-brand® 1.5~50ml Microprocessor Centrifuge “Cef-D50.6”, Safety Interlock, Max. 4000rpm, Digital Model with 6-Holes or 12- & 24-Holes Fixed Angle Rotor, 1.5~50ml 튜브용 디지털 원심분리기 **NEW**



NEW

Max. 4,000 rpm

2-Year Warranty

“Cef-D50.6” for 6 Tubes of 50ml, with 6 Holes Fixed Angle Rotor, 4000rpm



NEW

①TA50

(1) Fixed Angle Rotor ; 50ml 6Holes, “R5006”



NEW

②TA15

(2) Fixed Angle Rotor ; 10~15ml 12Holes, “R1512”



NEW

③TA15

(3) Fixed Angle Rotor ; 10~15ml 24Holes, “R1524”



NEW

*1.5/2ml ; ⑥+④

(4) Swing Rotor ; 4×50ml, 12×1.5/2ml & 10~15ml, 16×5~7ml “SR1550” Included ⑤,⑥,⑦ / Option ④



NEW

④TA2

①TA50 ②TA15

Optional Tube Adapters

- **Made in Korea**
- **Durable and Maintenance Free - Brushless DC Motor**
- **Ideal for Biology, Medicine, Pharmacology, Laboratory, etc. Various Application**
- **with 6-Holes or 12- & 24-Holes Fixed Angle Rotor for 1.5ml ~ 50ml Tubes ; On Adapters Adjustable 1.5/2ml, 5~7ml, 10~15ml, and 50ml**
- **Automatic Quick Self-Cooling by Fan**
- **Interchangeable Rotor**
- * Compact Design with Automatic Door Release.
- * Easy to Use Controls and Display
- * Self-diagnostic Function : Lid Opening, Unbalance, Over-Heat/ Current/ Voltage/ Speed
- * Auto-balancing System for Extend Motor Life and Reduce Noise
- * Program Memory Function : 9Set.
- * Precision Digital Timer, Set to 10Sec. / Max 30 Min
- * Pushing the Function Key for Short Runs
- * Rapid Deceleration due to Automatic Brake System

Specifications & Ordering information

Model		“Cef-D50.6”	
Spec.		6 Holes - 50ml or 12/24 Holes - 1.5~50ml	
Fixed Angle Rotor&Capa.	Included	(1) 6Hole ; 50ml Tubes	
	Option	(2) 12Hole ; (1.5~15)ml Tubes, (3) 24Hole ; (1.5~15)ml Tubes	
Swing Rotor & Capa.	Option	(4) SR1550 ; ⑤ 4×1Hole - 50ml, ⑥ 4×3Hole - 10~15ml, ⑦ 4×4Hole - 5~7ml, ⑧+④ 4×3Hole : 1.5/2.0ml	
		(1) 6 Tubes ; 50ml	
Useful Tube size & Acceptance	Option	When Option Fixed Angle Rotor	When Option Swing Rotor ;
		(2) 12 Tubes ; 1.5~15ml (3) 24 Tubes ; 1.5~15ml	(4) SR1550 ⑤ 4 Tubes : 50ml, ⑥ 12 Tubes : 10~15ml ⑦ 16 Tubes : 5~7ml ⑧+④ 12 Tubes : 1.5/2.0ml
Adapter and Size	Included	① 6ea×50ml Tubes, Size ; id30.7×L104mm	
	Option	When Option Fixed Angle Rotor ② 12/24ea×10~15ml Tubes Size ; id17.5×L95mm ③ 12/24ea×5~7ml Tubes Size ; id13.5×L69mm ④ 12/24ea×1.5/2ml Tubes Size ; id11×L42mm	When Option Swing Rotor ; ⑤ 4×1Hole - 50ml Tubes ⑥ 4×3Hole - 10~15ml Tubes ⑦ 4×4Hole - 5~7ml Tubes ⑧+④ 4×3Hole - 1.5/2.0ml Tubes
Speed Range (rpm) & RCF		600~4000rpm & 2,325×g (Swing Rotor ; 2,683×g)	
Motor		Brushless DC Motor	
Timer		0~30min	
Dimension & Weight		390×505×290mm, 19.8kg, Gross. 21.8kg	
Electric Reqts.		AC 230V, 50/60Hz or AC 120V, 60Hz	

Cat. No.	230V	DH.CefD0030
	120V	DH.CefD0130
Price, Each. ₩		

* Other Specifications are available upon Customer's Request.

Spare Rotor and Tube Adapters

		Ea. Price, ₩
DH.CefR5006	(1) 50ml 6Holes Angle Rotor “R5006” with 6ea×50ml Tube Adapter PP “TA50”, idφ 30.7×L104mm, for “Cef-50.6” & “Cef-D50.6”	
DH.CefA050	① 50ml Tube Adapter PP “TA50”, idφ 30.7×L104mm, Fit to Rotor “R5006”, for Centrifuge “Cef-50.6” & “Cef-D50.6”	
DH.CefA015	② 10~15ml Tube Adapter PP “TA15”, idφ 17.5×L98mm, for Centrifuge “Cef-6” & “Cef-8”, and Rotor “R1512” & “R1524”	

Optional Rotor and Tube Adapters

		Ea. Price, ₩
DH.CefR1512	(2) 10~15ml 12Holes Angle Rotor “R1512”, with 12ea×10/15ml Tube Adapter “TA15”, idφ 17.5×L98mm, for Centrifuge “Cef-50.6” & “Cef-D50.6”	
DH.CefR1524	(3) 10~15ml 24Holes Angle Rotor “R1524”, with 24ea×10/15ml Tube Adapter “TA15”, idφ 17.5×L98mm, for Centrifuge “Cef-50.6” & “Cef-D50.6”	
DH.CefSR1550	(4) Swing Rotor “SR1550”, with Tube Adapter PP 1Hole×4ea×50ml “TA5001”, 3Hole×4ea×1.5/2ml & 10~15ml “TA1503” and 4Hole×4ea×5~7ml “TA704”, for Centrifuge “Cef-D50.6”	
DH.CefA007	③ 5~7ml Tube Adapter PP “TA7”, idφ 13.5×L69mm, Fit to “TA15”, Tube Adapter, for Centrifuge “Cef-6”, “Cef-8”, “Cef-50.6”, and “Cef-D50.6”	
DH.CefA002	④ 1.5/2ml Tube Adapter PP “TA2”, idφ 11×L42mm, Fit to “TA15”, “TA1503” Tube Adapter, for Centrifuge “Cef-6”, “Cef-8”, “Cef-50.6”, and “Cef-D50.6”	
DH.CefA5001	⑤ 50ml Tube Adapter PP “TA5001”, Fit to Rotor “SR1550”, for Centrifuge “Cef-D50.6”	
DH.CefA1503	⑥ 10~15ml 3Hole Tube Adapter PP “TA1503”, Fit to Rotor “SR1550”, for Centrifuge “Cef-D50.6”	
DH.CefA704	⑦ 5~7ml 4Hole Tube Adapter PP “TA704”, Fit to Rotor “SR1550”, for Centrifuge “Cef-D50.6”	