

## Swing-out Rotor, GRS-G-r750-4

4 loadings  
 $\leq 90^\circ$

Only for 1580, 1580R



### Rectangular 750 ml Bucket GLB-r750-r750

Bucket bore (w x d x h, mm) : 99 x 99 x 98  
 Radius (mm) : 200  
 Max.RPM : 3,600  
 Max.RCF (g-force) : 2,898  
 Max.height for tube fit(mm) : 135

Tube										
Tube capacity (ml)	3	5	10	15	15 ml conical	50	50 ml conical	250	250 ml conical	500 ml conical
Tube rack										
Cat. No.	GAM-5-30(r750)		GAM-15-20(r750)		GAM-c15-16(r750)	GAM-50-8(r750)	GAM-c50-5(r750)	GAS-250(r750)	GAS-c250(r750)	GAS-c500(r750)
Rack capacity (ea/4)	30/120		20/80		16/64	8/32	5/20	1/4	1/4	1/4
Hole dimension (ΦxL, mm)	13 x 56.5	13 x 85	17.2 x 85		17.5 x 85	29.5 x 85	29.5 x 85	62.5 x 87	61 x 93	98 x 94



### Round 500 ml Bucket GLB-500-r750

Bucket bore (Φ x L, mm) : 69.2 x 135  
 Radius (mm) : 218  
 Max.RPM : 3,600  
 Max.RCF (g-force) : 3,159  
 Max.height for tube fit (mm) : 165

Tube	
Tube capacity (ml)	500
Bucket capacity (ea/4)	1/4



### Microplate Holder GLP-mw-r750

Holder bore (w x d x h, mm)  
 : 88 x 128.5 x 80  
 Radius (mm) : 171.5  
 Max.RPM : 3,600  
 Max.RCF (g-force) : 2,485

Plate		
Plate capacity (ml)	MTP	DWP
Holder capacity (ea/4)	4/16	1/4