

1248 · 1248R · 1236R · 1580 · 1580R

## Swing-out Rotor, GRS-G-750-4

4 loadings  
 $\leq 90^\circ$

Only for 1580, 1580R



\* GLB-b750-750 includes cap.



### Round 750 ml Bucket with Cap GLB-b750-750/ GLB-750-750

Bucket bore ( $\Phi$  x L, mm) : 99 x 101.5  
 Radius (mm) : 205  
 Max. RPM : 4,000  
 Max. RCF (g-force) : 3,667  
 Max. height for tube fit (mm) :  
 130 (w/ cap) / 142 (w/o cap)

Tube											
Tube capacity (ml)	3	5	10	15	15 ml conical	50	50 ml conical	250	250 ml conical	500 ml conical	750
Tube rack											None
Cat. No.	GAM-5-24(750)		GAM-10-21(750)	GAM-15-19(750)	GAM-c15-14(750)	GAM-50-7(750)	GAM-c50-5(750)	GAS-250(750)	GAS-c250(750)	GAS-c500(750)	-
Rack capacity (ea/4)	24/96		21/84	19/76	14/56	7/28	5/20	1/4	1/4	1/4	1/4
Hole dimension ( $\Phi$ xL, mm)	13.2 x 58	13.2 x 85	16 x 85	17.2 x 85	17 x 85	29.2 x 87	29.2 x 88	62.3 x 87	60.5 x 125	95.6 x 58	-



### Round 500 ml Bucket GLB-500-750

Bucket bore ( $\Phi$  x L, mm) : 69.2 x 135  
 Radius (mm) : 218  
 Max.RPM : 4,000  
 Max.RCF (g-force) : 3,900  
 Max.height for tube fit (mm) : 165

Tube	
Tube capacity (ml)	500
Bucket capacity (ea/4)	1/4



### Microplate Holder GLP-mw-750

Holder bore (w x d x h, mm)  
 : 88 x 128.5 x 80  
 Radius (mm) : 171.5  
 Max.RPM : 4,000  
 Max.RCF (g-force) : 3,068

Plate		
Plate capacity (ml)	MTP	DWP
Holder capacity (ea/4)	4/16	1/4