





Fixed Angle Rotor, GRE-M-s0.2-64


8 x 8-Tube PCR strips, 64 x 0.2 ml
 $\angle 45^\circ$
 Hole diameter (mm) : 6.5
 Max. height for tube fit (mm) : 16

Tube		
Tube capacity (ml)	0.2	8-Strip tube
Radius (mm)	1st : 58.6 / 2nd : 67.1	
Max.RPM	12,500	
Max.RCF (g-force)	1st : 10,237 / 2nd : 11,722	



Fixed Angle Rotor, GRE-M-m5.0-12

12 x 5.0 ml
 $\angle 45^\circ$
 Hole diameter (mm) : 17
 Max. height for tube fit (mm) : 68

Tube	
Tube capacity (ml)	5.0
Adaptor	None
Cat No.	-
Adaptor bore ($\Phi \times L$, mm)	-
Radius (mm)	91.3
Max.RPM	15,000
Max.RCF (g-force)	22,967








Bucket,
GLB-m2.0(8)



Swing-out Rotor, GRD-M-m2.0-8

8 x 1.5/2.0 ml
 $\angle 90^\circ$
 Hole diameter (mm) : 11.1
 Max. height for tube fit (mm) : 48

Tube			
Tube capacity (ml)	0.2	0.5	1.5/2.0
Adaptor			None
Cat No.	GAS-m0.2(2)	GAS-m0.5(2)	-
Adaptor bore ($\Phi \times L$, mm)	6.5 x 23	8 x 31	-
Radius (mm)	68.5	76.5	86.5
Max.RPM	13,000		
Max.RCF (g-force)	12,943	14,454	16,343








Bucket,
GLB-m2.0-4(16)



Swing-out Rotor, GRD-M-m2.0-16

16 x 1.5/2.0 ml
 $\angle 90^\circ$
 Hole diameter (mm) : 11.1
 Max. height for tube fit (mm) : 43

Tube			
Tube capacity (ml)	0.2	0.5	1.5/2.0
Adaptor			None
Cat No.	GAS-m0.2(2)	GAS-m0.5(2)	-
Adaptor bore ($\Phi \times L$, mm)	6.5 x 23	8 x 31	-
Radius (mm)	66	74	83
Max.RPM	13,000		
Max.RCF (g-force)	12,470	13,982	15,682