

## Manifold



Cat. No.	<b>HC-MFB-4V</b>
Details	4-Valve Manifold Basic with four rubber valves on a stainless steel bar, 30 cm



Cat. No.	<b>HC-MFB-6V</b>
Details	6-Valve Manifold Basic with six rubber valves on a stainless steel bar, 30 cm



Cat. No.	<b>HC-MFE-4V</b>
Details	4-Valve Manifold Extension with four rubber valves on a stainless steel bar, 20 cm



Cat. No.	<b>HC-MFE-6V</b>
Details	6-Valve Manifold Extension with six rubber valves on a stainless steel bar, 20 cm



Cat. No.	<b>HC-MFB-8V</b>
Details	8-Valve Manifold Basic with 8 rubber valves on a stainless steel bar, 30 cm

## Chamber and Rack



Cat. No.	<b>HC-CH30P</b>
Details	Acrylic Chamber Trunk and Plain Top, ø30 cm, height 40 cm



Cat. No.	<b>HC-CH30-4V</b>
Details	Acrylic Chamber Trunk and Top with 4 Rubber Valves, ø30 cm, height 40 cm



Cat. No.	<b>HC-CR25</b>
Details	Stainless Steel Rack with 3 Sets of SS Shelves and Trays, ø25cm (Trays can be inserted up to 5)

Cat. No.	<b>HC-CR-TS</b>
Details	A Set of a Tray and a Shelf



Cat. No.	<b>HC-CH30-8V</b>
Details	Acrylic Chamber Trunk and Top with 8 Rubber Valves, ø30 cm, height 40 cm

## Flask and others

Cat. No.	Details
<b>HC-GF40</b>	Freeze Drying Glass Flask 40 ml with rubber lid and stainless steel connector
<b>HC-GF80</b>	Freeze Drying Glass Flask 80 ml with rubber lid and stainless steel connector
<b>HC-GF120</b>	Freeze Drying Glass Flask 120 ml with rubber lid and stainless steel connector
<b>HC-GF150</b>	Freeze Drying Glass Flask 150 ml with rubber lid and stainless steel connector
<b>HC-GF300</b>	Freeze Drying Glass Flask 300 ml with rubber lid and stainless steel connector
<b>HC-GF600</b>	Freeze Drying Glass Flask 600 ml with rubber lid and stainless steel connector
<b>HC-GF900</b>	Freeze Drying Glass Flask 900 ml with rubber lid and stainless steel connector
<b>HC-GF1200</b>	Freeze Drying Glass Flask 1200 ml with rubber lid and stainless steel connector
<b>HC-GFT34</b>	Rubber lid for 34 mm diameter Flask (Glass Flask 40 ~ 80 ml)
<b>HC-GFT60</b>	Rubber lid for 60 mm diameter Flask (Glass Flask 120 ~ 300 ml)
<b>HC-GFT90</b>	Rubber lid for 90 mm diameter Flask (Glass Flask 600 ~ 1200 ml)
<b>V04CS12250-00</b>	Stainless Steel connector
<b>HC-AA</b>	Acetal Adaptor for the connection Vacuum Hose to Rubber Valve
<b>HC-VH</b>	Vacuum Hose with 2 Clamps, 100 cm
<b>GVP-W2V20</b>	High Vacuum Rotary Vane Pump, 0.4 kW(0.5 HP), 200 L/min, 1X10-3 torr
<b>GVP-WOF150</b>	Oil Mist Trap