
















Cover Plates for HyperCOOL

<p>HHC-CPP HC3055, HC3110 Trap Plate for Connection Vacuum Hose to Vacuum Concentrator</p> 	<p>HHC-CPB HC3055, HC3110 Acrylic Base for Manifold or Chamber</p> 	<p>HHC-CPM HC3055, HC3110 Acrylic Base for HHC-MFB-8V</p> 	<p>HHC-CPP(8) HC8080 Trap Plate for Connection Vacuum Hose to Vacuum Concentrator</p> 	<p>HHC-CPB(8) HC8080 Acrylic Base for Manifold or Chamber</p> 	<p>HHC-CPM(8) HC8080 Acrylic Base for HHC-MFB-8V</p> 
---	---	--	--	---	---


Manifolds for HyperCOOL

<p>HHC-MFB-4V Incl. 4 rubber valves on a stainless steel bar, 30 cm</p> 	<p>HHC-MFB-6V Incl. 6 rubber valves on a stainless steel bar, 30 cm</p> 	<p>HHC-MFE-4V for extension Incl. 4 rubber valves on a stainless steel bar, 20 cm</p> 	<p>HHC-MFE-6V for extension Incl. 6 rubber valves on a stainless steel bar, 20 cm</p> 	<p>HHC-MFB-8V Incl. 8 rubber valves on a stainless steel bar, 30 cm</p> 
--	--	--	--	---

Chambers for HyperCOOL

<p>HHC-CH30P Acrylic Chamber Trunk and Plain Top, ø30 cm, height 40 cm</p> 	<p>HHC-CH30-4V Acrylic Chamber Trunk and Top with 4 rubber valves, ø30 cm, height 40 cm</p> 	<p>HHC-CH30-8V Acrylic Chamber Trunk and Top with 8 Rubber Valves, ø30 cm, height 40 cm</p> 	<p>Stoppering Assembly</p> 
---	--	--	---

Racks For HyperCOOL

<p>HHC-CR25 Stainless Steel Rack with 3 sets of shelves and trays, ø25cm (Trays can be inserted up to 5)</p> 	<p>HHC-CR-TS A Set of a Tray and a Shelf</p> 	<p>HC-HP6003 Heating Plate (basic 3 shelves)</p> 	<p>HC-HP6005 Heating Plate (5 shelves)</p> 	<p>HC-HPS Heating Plate (1shelf for additional order)</p> 
---	---	---	---	--