

Accessories Z287-A

Rotor/Bucket

Order No.:
Z287-0450H



Swing out rotor 4 x 50 ml
Angle: 0-75°

Adapter

Acceleration in s: 26/242
Deceleration in s: 33/252
max. speed: 5,000 rpm
RCF-value: 3,633 xg
max. radius: 13.0 cm
max. Ø: 29 mm

Order No.:	Tube rack	Ø [mm]	Length (min./max.):
without adapter	1 x 50 ml conical	29	116
Z326-50-B15	1 x 15 ml conical	17	120
Z326-15-A7*	1 x 7 ml	13.5	95/115
Z326-15-A5*	1 x 5 ml	13.5	65/90

* only possible with adapter Z326-50-B15

Order No.:
Z287-0430H



Swing out rotor 4 x 30 ml Universal
Angle: 0-90°

Acceleration in s: 26/241
Deceleration in s: 31/250
max. speed: 5,000 rpm
RCF-value: 3,437 xg
max. radius: 12.3 cm
max. Ø: 25 mm

Order No.:	Tube rack	Ø [mm]	Length (min./max.):
without adapter	1 x 30 ml skirted	25	95
without adapter	1 x 25 ml skirted	25	90

Order No.:
Z287-0810H



Swing out rotor 8 x 10 ml
for blood collection tubes
Angle: 0-90°

Acceleration in s: 25/240
Deceleration in s: 32/253
max. speed: 5,000 rpm
RCF-value: 3,717 xg
max. radius: 13.3 cm
max. Ø: 16 mm

Order No.:	Tube rack	Ø [mm]	Length (min./max.):
Without	1 x 6-10 ml Vacutainer®	16	100
Z326-0810-A7	1 x 1.8-7 ml Vacutainer®	13	75/100

Order No.:
Z287-02MP



Swing out rotor 2 x Microtitre plates
Angle: 0-90°

Acceleration in s: 27/182
Deceleration in s: 29/193
max. speed: 3,800 rpm
RCF-value: 1,453 xg
max. radius: 9.0 cm
max. loading height: 20 mm
max. loading weight: 100 g

Order No.:
Z287-0650



Angle rotor 6 x 50 ml
Angle: 40°

Acceleration in s: 34/293
Deceleration in s: 38/317
max. speed: 6,000 rpm
RCF-value: 4,427 xg
max. radius: 11.0 cm
max. Ø: 29 mm

Order No.:	Tube rack	Ø [mm]	Length (min./max.):
without adapter	1 x 50 ml conical	29	116
without adapter	1 x 50 ml	29	100/120
Z206-50-A15	1 x 15 ml conical	17	120
Z206-50-A57	1 x 7 ml	13	95/115
Z206-50-A57C*	1 x 5 ml	13	65/90

* With Z206-50-A57

Order No.:
Z287-1215



Angle rotor 12 x 15 ml
Angle: 32°

Acceleration in s.: 34/295
Deceleration in s: 38/317
max. speed: 6,000 rpm
RCF-value: 4,427 xg
max. radius: 11.0 cm
max. Ø: 17 mm

Order No.:	Tube rack	Ø [mm]	Length (min./max.):
without adapter	1 x 15 ml conical	17	120
without adapter	1 x 15 ml glass	17	105/120
Z326-15-A7	1 x 7 ml	13	95/115
Z326-15-A5	1 x 5 ml	13	65/90