

Accessories Z326 and Z326-K

Rotor/Bucket

Order No.:
Z306-100



Swing out rotor 4 place
Angle: 0-90°

Adapter

Acceleration in s: 15/100
Deceleration in s: 15/150
max. Speed: 4500 rpm
RCF-value: 3350 xg
max. Radius: 14.8 cm
Temp. at max. speed: -1°C

Volume	145 ml	100 ml	85 ml	50 ml	50 ml
Tubes ø in mm	Nalgene® 50	RB Glass 44	RB/OR 38	RB Glass 29	Falcon® 29
Length min./max. in mm	100	90/1	90/108	90/118	116
Tubes per rotor	4	4	4	4	4
Radius correction (cm)	1.0	1.0	0.8	0.7	0.3
Order-No.: Z306-100-	A145	A100	A85	A50R	A50

Volume

Tubes ø in mm

Length min./max. (mm)
Tubes per rotor
Radius Correction (cm)
Order No. Tube rack

Volume	50 ml skirted 29	30 ml Universal 25	15 ml Falcon® 17	6-10 ml Vakut.® 16	1.8-7 ml Vakut.® 13	1.5 ml Reakt. 11
Length min./max. (mm)	116	95/105	120	90/108	75/100	42
Tubes per rotor	4	4	8	28	28	40
Radius Correction (cm)	0.6	1.1	0.0	0.4	0.7	5.5
Order No. Tube rack	A50SS	A30	A15	A10	A57	A20

Order No.:
Z326-100H

Swing out rotor 4 Places
w/ sealed buckets
Angle: 0-90°

Z326-100H-BUK
Bucket for Tube Rack w/ lid

Z326-100H-LID
Lid for bucket



Acceleration in s: 15/100
Deceleration in s: 15/150
max. Speed: 5000 rpm
RCF-value: 4080 xg
max. Radius: 14.6 cm
Temp. at max. speed: 2°C

Volume	100 ml RB Glass 40	85 ml RB/OR 38	50 ml RB/OR 29	50 ml Falcon® 29
Length min./max. in mm	90/108	90/108	90/133	116
Tubes per rotor	4	4	4	4
Radius correction (cm)	0.9	0.6	0.6	0.4
Order-No.: Z326-100H-	A100	A85	A50R	A50

Volume

Tubes ø in mm

Length min./max. (mm)
Tubes per rotor
Radius Correction (cm)
Order No. Tube rack

Volume	50 ml skirted 29	30 ml Universal 25	15 ml Falcon® 17	15 ml Falcon® 17	15 ml RB Glass 17	6-10 ml Vakut.® 16	10-15ml Vakut.® 16	1.8-7 ml Vakut.® 13	1.5 ml Reakt. 11	50ml Falcon® 29	15ml Falcon® 17
Length min./max. (mm)	116	95/105	120	120	90/108	75/100	75/125	75/100	42	116	120
Tubes per rotor	4	4	4	8	16	16	4	16	20	8	12
Radius Correction (cm)	0.7	1.5	0.5	0.5	0.6	0.6	0.6	0.6	0.6	0.0	0.0
Order No. Tube rack	A50SS	A30	A15S	A15*	A15R	A10	A15L*	A57	A20	B50	B15

* only without bucket lid

Order No.:
Z326-02MP



Swing out rotor 2 x 3 Microplates
Angle: 0-90°

Acceleration in s: 20/160
Deceleration in s: 15/360
max. Speed: 4500 rpm
RCF-value: 2716 xg
max. Radius: 12.0 cm
max. Loading height: 63 mm
max. Loading weight: 310 g
Temp. at max. speed: 0°C

Order No.:
BT1500-A1520
BT1500-A05
Z326-MPCA

Tube rack
20 x 1.5 ml (2.0 ml) Tubes
20 x 0.5 ml Tubes
3 x Chamber slide or 35/60 mm petri dish

Order No.:
Z326-3015



Angle rotor 30 x 15 ml
Angle: 35°

Acceleration in s: 15/160
Deceleration in s: 10/380
max. Speed: 4500 rpm
RCF-value: 2830/2467 xg
max. Radius: 12.5/10.9 cm
max. Ø: 17 mm
Temp. at max. speed: -6°C

Order No.:	Tube rack	Ø (mm)	Length (min./max.):
without	1 x 15 ml-Glass	17.0	95/115
C3100-ADP	1 x 5/7 ml (pack of 8)	13	75/100