

# Accessories Z326 and Z326-K

## Rotor/Bucket

Order No.:  
Z326-2010



Angle rotor 20 x 10 ml  
Angle: 30°

## Adapter

Acceleration in s: 40/360  
Deceleration in s: 30/570  
Max. speed: 12,000 rpm  
Max. RCF: 15,775 xg  
Max. radius: 9.8 cm  
Max. Ø: 16 mm  
Temp. at max. speed: 7° C

Order No.:	Tube rack	Ø (mm)	Length (min./max.):
without Adapter	1 x 10 ml	16	80

Order No.:  
Z326-3020H



Angle rotor 30 x 1.5 / 2.0 ml  
Angle: 45°

Acceleration in s: 25/200  
Deceleration in s: 25/360  
Acceleration in s: 25/210  
Deceleration in s: 30/360  
Max. speed: 13,000 rpm  
Max. speed: 14,000 rpm  
Max. RCF: 17,758 xg  
Max. RCF: 20,595 xg  
Max. radius: 9.4 cm  
Max. Ø: 11 mm  
Temp. at max. speed: 9° C

Order No.:	Tube rack	Ø (mm)	Length (min./max.):
without	1 x 2,0 ml	11	40
without	1 x 1,5 ml	11	40
C1008-A5-6	1 x 0.5 ml	8	45
C1008-A2-6	1 x 0.4/0.2 ml PCR	6	45

Order No.:  
Z326-2420



Angle rotor 24 x 1.5 / 2.0 ml  
Angle: 45°

Acceleration in s: 23/210  
Deceleration in s: 16/240  
Acceleration in s: 25/230  
Deceleration in s: 17/420  
Max. speed: 14,000 rpm  
Max. speed: 15,000 rpm  
Max. RCF: 18,624 xg  
Max. RCF: 21,379 xg  
Max. radius: 8.5 cm  
Max. Ø: 11 mm  
Temp. at max. speed: 7° C

Order No.:	Tube rack	Ø (mm)	Length (min./max.):
without	1 x 2,0 ml	11	40
without	1 x 1,5 ml	11	40
C1008-A5-6	1 x 0.5 ml	8	45
C1008-A2-6	1 x 0.4/0.2 ml PCR	6	45

Order No.:  
Z326-2420H



Angle rotor 24 x 1.5 / 2.0 ml  
Angle: 45° | hermetically sealed

Acceleration in s: 23/240  
Deceleration in s: 16/240  
Acceleration in s: 25/230  
Deceleration in s: 17/420  
Max. speed: 14,000 rpm  
Max. speed: 15,000 rpm  
Max. RCF: 18,624 xg  
Max. RCF: 21,379 xg  
Max. radius: 8.5 cm  
Max. Ø: 11 mm  
Temp. at max. speed: 7° C

Order No.:	Tube rack	Ø (mm)	Length (min./max.):
without	1 x 2,0 ml	11	40
without	1 x 1,5 ml	11	40
C1008-A5-6	1 x 0.5 ml	8	45
C1008-A2-6	1 x 0.4/0.2 ml PCR	6	45

Order No.:  
Z326-1220H



Angle rotor 12 x 1.5 / 2.0 ml  
Angle: 40°

Acceleration in s: 25/240  
Deceleration in s: 20/210  
Max. speed: 18,000 rpm  
Max. RCF: 23,542 xg  
Max. radius: 6.5 cm  
Max. Ø: 11 mm  
Temp. at max. speed: 3° C

Order No.:	Tube rack
Z36-04-HS	0.4 ml Tubes (Ø 6 x 50 mm) Adapter Kit (6 Pieces)
Z36-05-HS	0.5 ml Tubes (Ø 8 x 32 mm) Adapter Kit (6 Pieces)
Z36-20-HS	1.5 ml Adapter for full performance (necessary from 16,000 xg on) (6 Pieces)

Order No.:  
Z326-4420



Angle rotor 44 x 1.5 / 2.0 ml  
Angle: 32°/55°

Acceleration in s: 28/256  
Deceleration in s: 21/434  
Max. speed: 15,000 rpm  
Max. RCF: 21,379 xg  
Max. radius: 8.5 cm  
Max. Ø: 11 mm  
Temp. at max. speed: 8° C

Order No.:	Tube rack	Ø (mm)	Length (min./max.):
without	1 x 2,0 ml	11	40
without	1 x 1,5 ml	11	40
C1008-A5-6	1 x 0.5 ml	8	45
C1008-A2-6	1 x 0.4/0.2 ml PCR	6	45