

# Accessories Z326 and Z326-K

## Rotor/Bucket

Order No.:  
Z326-1215



Angle rotor 12 x 15 ml  
Angle: 32°

## Adapter

Acceleration in s: 13/88  
Deceleration in s: 11/222  
max. Speed: 6000 rpm  
RCF-value: 4427 xg  
max. Radius: 11.0 cm  
max. Ø: 17 mm  
Temp. at max. speed: -4°C

Volume	15 ml Falcon®	15 ml	7 ml	5 ml
Ø Tubes in mm	17	17	13	13
Length min./max. in mm	120	105-120	100	75
Adapter Order No.:	without	without	C3100-ADP	C3100-ADP

Order No.:  
Z326-0650-LS



Angle rotor 6 x 50 ml  
Angle: 40°

Acceleration in s: 13/89  
Deceleration in s: 11/239  
max. Speed: 6000 rpm  
RCF-value: 4427 xg  
max. Radius: 11.0 cm  
max. Ø: 29 mm  
Temp. at max. speed: -3°C

Volume	50 ml Falcon®	50 ml RB/OR	15 ml Falcon®	7 ml	5 ml
Ø Tubes in mm	29	29	17	13	13
Length min./max. in mm	116	100/120	120	100	75
Adapter Order No.:	without	without	Z206-50-A15	Z206-50-A57	Z206-50-A57C*

\*with Z206-50-A57

Order No.:  
Z326-0685-25



Angle rotor 6 x 85 ml  
Super rotor 85ml, 50ml, 15ml, and 7ml  
Angle: 25°

Acceleration in s: 40/400  
Deceleration in s: 40/960  
Acceleration in s: 60/500  
Deceleration in s: 50/1,260  
Max. speed: 11,000 rpm  
Max. speed: 13,500 rpm  
Max. RCF: 13,932 xg  
Max. RCF: 20,984 xg  
Max. radius: 10.3 cm  
Max. Ø: 38 mm  
Temp. at max. speed: 19°C

Order No.:	Tube rack	Ø (mm)	Length (min./max.):
without Adapter	1 x 85 ml	38	113
Z326-85-A50R	1 x 50 ml	29	105
Z326-85-A50	1 x 50 ml conical	29	116
Z326-85-A30	1 x 30 ml	25	90/103
Z326-85-A15R	1 x 15 ml	17	103/110
Z326-85-A15	1 x 15 ml conical	17	120

Order No.:  
Z326-0485



Angle rotor 4 x 85 ml  
Angle: 30°

Acceleration in s: 60/300  
Deceleration in s: 40/820  
Max. speed: 12,000 rpm  
Max. RCF: 14,809 xg  
Max. radius: 9.2 cm  
Max. Ø: 38 mm  
Temp. at max. speed: 6°C

Order No.:	Tube rack	Ø (mm)	Length (min./max.):
without Adapter	1 x 85 ml	38	113
Z326-85-A50R	1 x 50 ml	29	105
Z326-85-A50	1 x 50 ml conical	29	116
Z326-85-A30	1 x 30 ml	25	90/103
Z326-85-A15R	1 x 15 ml	17	103/110
Z326-85-A15	1 x 15 ml conical	17	120

Order No.:  
Z326-0650-HS



Angle rotor 6 x 50 ml (round)  
Angle: 26°

Acceleration in s: 40/360  
Deceleration in s: 30/570  
Max. speed: 12,000 rpm  
Max. RCF: 13,522 xg  
Max. radius: 8.4 cm  
Max. Ø: 29 mm  
Temp. at max. speed: 1°C

Order No.:	Tube rack	Ø (mm)	Length (min./max.):
without Adapter	1 x 50 ml	29	95/115
Z326-50-A30	1 x 30	25	92/95
Z326-50-B15R	1 x 15 ml	17	100/105
Z326-50-A15R	1 x 15 ml conical*	17	120

\*only without rotor lid

Order No.:  
Z326-1050



Angle rotor 10 x 50 ml conical  
Angle: 38°

Acceleration in s: 63/380  
Deceleration in s: 37/796  
Max. speed: 7,500 rpm  
Max. RCF: 8,141 xg  
Max. radius: 13 cm  
Max. ø: 29 mm  
Temp. at max. speed: 2°C

Order No.:	Adapter	ø (mm)	Length (min./max.):
Z326-50-B15HS	1 x 15 ml RB	17	97/123
Z326-15-A7*	1 x 7 ml	13.5	95/115
Z326-15-A5*	1 x 5 ml	13.5	70/90
Z326-50-A15	1 x 15 ml conical	17	120

\*only possible with adapter Z326-50-A15 or Z326-50-B15