

High Speed Rotors:



Item: Z366-06250-36

6 x 250ml Rotor (28°)

Max Speed: 10,000 rpm / 15,650 x g

Accel: 82 sec. / Decel: 130 sec.

Inserts/Adapters

Z366-06250-A15: 4 x 15ml conical

Z366-06250-A50R: 50ml round

Z366-06250-A50: 50ml conical



Item: Z326-0685-36

6 x 85ml Rotor (38°)

Max Speed: 13,000 rpm / 21,726 x g

Accel: 60 sec. / Decel: 70 sec.

Inserts/Adapters

Z326-85-A15R: 15ml round

Z326-85-A15: 15ml conical

Z326-85-A50R: 50ml round

Z326-85-A50: 50ml conical



Item: Z326-0485-36

4 x 85ml Rotor (30°)

Max Speed: 20,000 rpm / 41,137 x g

Accel: 42 sec. / Decel: 52 sec.

Inserts/Adapters

Z326-85-A15R: 15ml round

Z326-85-A15: 15ml conical

Z326-85-A50R: 50ml round

Z326-85-A50: 50ml conical



Item: Z326-1050-36

10 x 50ml Conical Rotor (30°)

Max Speed: 10,500 rpm / 16,022 x g

Accel: 86 sec. / Decel: 63 sec.

Inserts/Adapters

Z326-50-A15: 15ml conical

Z326-50-B15: 15ml round

Z326-15-A7: 7ml (only with 15ml adapter)

Z326-15-A5: 5ml (only with 15ml adapter)



Item: Z326-0650-HS-36

6 x 50ml Round Rotor (26°)

Max Speed: 21,000 rpm / 41,410 x g

Accel: 50 sec. / Decel: 50 sec.

Inserts/Adapters

Z326-50-A30: 30ml round

Z326-50-A15R: 15ml (conical or round)



Item: Z326-2010

20 x 10ml Rotor (30°)

Max Speed: 16,000 rpm / 28,040 x g

Accel: 40 sec. / Decel: 30 sec.



Item: Z326-3020H-36

30 x 1.5/2.0ml Rotor (40°)
Hermetically Sealed Lid

Max Speed: 20,000 rpm / 42,032 x g

Accel: 55 sec. / Decel: 55 sec.



Item: Z326-1220-36

12 x 1.5/2.0ml Rotor (40°)

Max Speed: 30,000 rpm / 65,395 x g

Accel: 44 sec. / Decel: 70 sec.

Inserts/Adapters

Z36-04-HS: 0.4ml adapter kit

Z36-05-HS: 0.5ml adapter kit

Z36-20-HS: 1.5ml adapter
(Required from 16,000xg on)

Additional Rotors (Low Speed):



Item: Z326-3015-36

30 x 15ml Rotor (35°)

Max Speed: 4,500 rpm / 2,830 x g

Accel: 13 sec. / Decel: 17 sec.

Inserts/Adapters

C3100-ADP: 5-7ml (12-13mm)



Item: Z326-02MP-36

Swing Out Rotor
2 x 3 microplates (90°)

Max Speed: 4,500 rpm / 2,716 x g

Accel: 20 sec. / Decel: 25 sec.

Inserts

BT1500-A1520: 20 x 1.5ml

BT1500-A05: 20 x 0.5ml

Z326-MPCA: 3 x chamber slide and
dish carrier 2/pk



Z366-250-LID



Item: Z366-250-36

4 x 250ml Swing Out Rotor

Max Speed: 4,000 rpm / 2,987 x g

Accel: 20 sec. / Decel: 25 sec.

| Inserts: | Tube | qty/ insert | qty./ rotor |
|---------------|-------------------------------------|----------------|----------------|
| Z366-250-A250 | 250ml | 1 | 4 |
| Z366-250-A100 | 100ml | 1 | 4 |
| Z366-250-A50 | 50ml conical | 3 | 12 |
| Z366-250-A15 | 15ml conical | 7 | 28 |
| Z366-250-A10 | 10ml | 8 | 32 |
| Z366-250-A57 | 5/7ml | 14 | 56 |
| Z366-250-LID | Hermetically Sealed Lid, 2/pk | 1 | 4 |

New optional accessory!!!

Z326-MPCA
3 x chamber slide and dish carrier



Chamber Slides



35mm Dishes



60mm Dishes

Fits all Hermle microplate carriers!!!

*Inserts sold in 2/pk.
Rotor accepts 4 inserts (2 x 2/pk.)