

## Universal Swing Out Rotor:



### Item: Z366-250

4 x 250ml Swing Out Rotor

Max Speed: 4,500 rpm / 3,780 x g

Accel: 34 sec. / Decel: 36 sec.

Inserts:	Tube	qty/ insert	qty./ rotor
Z366-250-A250	250ml	1	4
Z366-250-A100	100ml	1	4
Z366-250-A50	50ml conical	3	12
Z366-250-A15	15ml conical	7	28
Z366-250-A10	10ml	8	32
Z366-250-A57	5/7ml	14	56
Z366-250-A20	1.5/2.0ml	9	36
Z366-250-LID	Hermetically Sealed Lid, 2/pk	1	4



Z366-250-LID



### Item: Z366-250-HC

4-place High Capacity Swing Out Rotor

Max Speed: 4,500 rpm / 3,735 x g

Accel: 34 sec. / Decel: 36 sec.

Inserts:	Tube	qty/ insert	qty./ rotor
Z366-250-B50	50ml conical	4	16
Z366-250-B15	15ml conical	10	40
Z366-250-B10	10ml	12	48
Z366-250-B57	5/7ml	14	56

\*Inserts sold in 2/pk.  
Rotor accepts 4 inserts (2 x 2/pk.)

## Additional Rotors:



### Item: Z366-06250

6 x 250ml Angle Rotor (28°)

Max Speed: 8,000 rpm / 10,016 x g

Accel: 130 sec. / Decel: 92 sec.



### Item: Z326-0685

6 x 85ml Angle Rotor (38°)

Max Speed: 11,000 rpm / 15,555 x g  
(Z366)

Max Speed: 13,000 rpm / 21,726 x g  
(Z366K)

Accel: 85 sec. / Decel: 70 sec.\*



### Item: Z326-0650-HS

6 x 50ml Angle Rotor (26°) Round

Max Speed: 13,000 rpm / 15,869 x g

Accel: 48 sec. / Decel: 49 sec.



### Item: Z326-1050

10 x 50ml Angle Rotor (38°) Conical

Max Speed: 9,000 rpm / 11,771 x g  
(Z366)

Max Speed: 10,500 rpm / 16,022 x g  
(Z366-K)

Accel: 22 sec. / Decel: 23 sec.\*

### Inserts/Adapters

Z366-06250-A15: 4 x 15ml conical

Z366-06250-A50R: 50ml round

Z366-06250-A50: 50ml conical

### Inserts/Adapters

Z326-85-A15R: 15ml round

Z326-85-A15: 15ml conical

Z326-85-A50R: 50ml round

Z326-85-A50: 50ml conical

### Inserts/Adapters

Z326-50-A30: 30ml round

Z326-50-A15R: 15ml (conical or round)

### Inserts/Adapters

Z326-50-A15: 15ml conical

Z326-50-B15: 15ml round

Z326-15-A7: 7ml (only with 15ml adapter)

Z326-15-A5: 5ml (only with 15ml adapter)

\*Acceleration and deceleration provided for the maximum speed of model Z366.