

# Accessories Z446 and Z446-K

## Rotor/Bucket

Order No.:  
Z326-0685



Angle rotor 6 x 85 ml  
Angle: 38°

## Adapter

Acceleration in s: 49/462  
Deceleration in s: 46/1,655  
Acceleration in s: 69/549  
Deceleration in s: 67/1,307  
max. speed: 11,000/13,000 rpm  
max. RCF: 15,555/21,726 xg  
max. radius: 11.5 cm  
max.  $\varnothing$ : 38 mm  
Temp. at max. speed: 8°C

Order No.:	Tube rack	$\varnothing$ (mm)	Length (min./max.):
without Adapter	1 x 85 ml	38	113
Z326-85-A50R	1 x 50 ml	29	105
Z326-85-A50	1 x 50 ml conical	29	116
Z326-85-A30	1 x 30 ml	25	90/103
Z326-85-A15R	1 x 15 ml	17	103/110
Z326-85-A15	1 x 15 ml conical	17	120

Order No.:  
Z326-0485



Angle rotor 4 x 85 ml  
Angle: 30°

Acceleration in s: 50/448  
Deceleration in s: 45/1,251  
Acceleration in s: 61/480  
Deceleration in s: 47/1,220  
max. speed: 15,000/16,000 rpm  
max. RCF: 23,140/26,328 xg  
max. radius: 9.2 cm  
max.  $\varnothing$ : 38 mm  
Temp. at max. speed: 7°C

Order No.:	Tube rack	$\varnothing$ (mm)	Length (min./max.):
without Adapter	1 x 85 ml	38	113
Z326-85-A50R	1 x 50 ml	29	105
Z326-85-A50	1 x 50 ml conical	29	116
Z326-85-A30	1 x 30 ml	25	90/103
Z326-85-A15R	1 x 15 ml	17	103/110
Z326-85-A15	1 x 15 ml conical	17	120

Order No.:  
Z326-06250



Angle rotor 6 x 250 ml  
Angle: 28°

Acceleration in s: 66/573  
Deceleration in s: 84/1,871  
max. speed: 8,000 rpm  
max. RCF: 10,016 xg  
max. radius: 14 cm  
max.  $\varnothing$ : 62 mm  
Temp. at max. speed: -1°C

Order No.:	Tube rack	$\varnothing$ (mm)	Length (min./max.):
without Adapter	1 x 250 ml	62	122
Z366-06250-A50	1 x 50 ml conical	29	118
Z366-06250-A50R	1 x 50 ml	29	103
Z366-06250-A30	2 x 30 ml	26	92
Z366-06250-A15	4 x 15 ml conical	17	120

Order No.:  
Z326-0650-HS



Angle rotor 6 x 50 ml (round)  
Angle: 26°

Acceleration in s: 28/263  
Deceleration in s: 31/922  
max. speed: 13,000 rpm  
max. RCF: 15,869 xg  
max. radius: 8.4 cm  
max.  $\varnothing$ : 29 mm  
Temp. at max. speed: -4°C

Order No.:	Tube rack	$\varnothing$ (mm)	Length (min./max.):
without Adapter	1 x 50 ml	29	95/115
Z326-50-A30	1 x 30	25	92/95
Z326-50-B15R	1 x 15 ml	17	100/105
Z326-50-A15R	1 x 15 ml conical*	17	120

\*only without rotor lid

Order No.:  
Z326-2010



Angle rotor 20 x 10 ml  
Angle: 30°

Acceleration in s: 32/305  
Deceleration in s: 37/984  
max. speed: 12,000 rpm  
max. RCF: 15,775 xg  
max. radius: 9.8 cm  
max.  $\varnothing$ : 16 mm  
Temp. at max. speed: -3°C

Order No.:	Tube rack	$\varnothing$ (mm)	Length (min./max.):
without Adapter	1 x 10 ml	16	80

Order No.:  
Z326-04500



Angle rotor 4 x 500 ml  
Angle: 24°

Acceleration in s: 73/575  
Deceleration in s: 84/2,317  
max. speed: 8,000 rpm  
max. RCF: 10,367 xg  
max. radius: 14.5 cm  
max.  $\varnothing$ : 69.5 mm  
Temp. at max. speed: 4°C

Order No.:	Tube rack	$\varnothing$ (mm)	Length (min./max.):
without Adapter	1 x 500 ml	69.5	165
Z466-500-A250	1 x 250 ml	62	122
Z446-500-A250F	1 x 250 ml Corning®	60	159
Z446-500-A225	1 x 175 ml Falcon®	61	118
Z446-500-A225	1 x 225 ml Falcon®	61	137
Z446-500-A50	1 x 50 ml conical	29	116
Z446-500-A15C	6 x 15 ml conical	17	120

Order No.:  
Z326-1050



Angle rotor 10 x 50 ml conical  
Angle: 38°

Acceleration in s: 60/480  
Deceleration in s: 68/1,747  
Acceleration in s: 61/480  
Deceleration in s: 480/1,747  
max. speed: 10,000/10,500 rpm  
max. RCF: 14,532/16,022 xg  
max. radius: 13 cm  
max.  $\varnothing$ : 29 mm  
Temp. at max. speed: 2°C

Order No.:	Adapter	$\varnothing$ (mm)	Length (min./max.):
Z326-50-B15HS	1 x 15 ml RB	17	97/123
Z326-15-A7*	1 x 7 ml	13.5	95/115
Z326-15-A5*	1 x 5 ml	13.5	70/90
Z326-50-A15	1 x 15 ml conical	17	120

\*only possible with adapter Z326-50-A15 or Z326-50-B15