

## Universal Swing Out Rotors:



Z446-750



Z446-750-MP



Z446-MP-BUK  
(Lid not included)



Z446-750-LID  
(Hermetically sealed lid  
with sealing ring)



Z446-MP-RA  
Microplate removing aid

Item: Z446-750-AC	
4 x 750ml Swing Out Rotor	
Max Speed: 4,000 rpm / 3,434 x g (Z446)	
Max Speed: 4,500 rpm / 4,346 x g (Z446-K)	
Accel: 47 sec. / Decel: 49 sec.	
Z446-750-AC	Rotor without buckets
Z446-750	Rotor complete with 4 round buckets
Z446-750-BUK	Round buckets, 2/pk.
Z446-MP-BUK	Rectangular buckets, 2/pk.
Z446-750-MP	Microplate carrier, 2/pk
Z446-MP-STK	PCR plate stacking adapter (for Z446-750-MP), 2/pk
Z446-750-LID	Hermetically sealed lid for round buckets, 2/pk
Z446-MP-LID	Hermetically sealed lid for rectangular buckets, 2/pk

Inserts: (for round buckets)	Tube/Bottle	qty/insert	qty./rotor
Z446-750-A500	500ml conical	1	4
Z446-750-A250	250ml bottle	1	4
Z446-750-A225	225ml conical	1	4
Z446-750-A50	50ml conical	7	28
Z446-750-A30	30ml round	8	32
Z446-750-A15	15ml conical	17	68
Z446-750-A10	10ml	18	72
Z446-750-A57	5/7ml	27	108

### New optional accessories!!!

#### Z326-MPCA

3 x chamber slide and dish carrier



Chamber Slides

35mm Dishes

60mm Dishes

#### Z446-MP-STK

PCR plate stacking adapter  
(fits Z446-750-MP Only)



## Additional Rotors:



#### Item: Z446-04500

4 x 500ml Angle Rotor (24°)  
Max Speed: 8,000 rpm / 10,367 x g  
Accel: 73 sec. / Decel: 82 sec.



#### Item: Z366-06250

6 x 250ml Angle Rotor (28°)  
Max Speed: 8,000 rpm / 10,016 x g  
Accel: 66 sec. / Decel: 84 sec.



#### Item: Z326-0685

6 x 85ml Angle Rotor (38°)  
Max Speed: 11,000 rpm / 15,555 x g (Z446)  
Max Speed: 13,000 rpm / 21,726 x g (Z446K)  
Accel: 48 sec. / Decel: 46 sec.



#### Item: Z326-0485

4 x 85ml Angle Rotor (30°)  
Max Speed: 15,000 rpm / 23,140 x g (Z446)  
Max Speed: 16,000 rpm / 26,328 x g (Z446K)  
Accel: 50 sec. / Decel: 45 sec.

#### Inserts/Adapters

Z446-500-A15: 15ml conical  
Z446-500-A50R: 50ml round  
Z446-500-A50: 50ml conical  
Z446-500-A250: 250ml bottle

#### Inserts/Adapters

Z366-06250-A15: 4 x 15ml conical  
Z366-06250-A50R: 50ml round  
Z366-06250-A50: 50ml conical

#### Inserts/Adapters

Z326-85-A15R: 15ml round  
Z326-85-A15: 15ml conical  
Z326-85-A50R: 50ml round  
Z326-85-A50: 50ml conical

#### Inserts/Adapters

Z326-85-A15R: 15ml round  
Z326-85-A15: 15ml conical  
Z326-85-A50R: 50ml round  
Z326-85-A50: 50ml conical